

**SPARE DIFFERENTIAL PRESSURE TRANSMITTERS FOR
FRONT-END EPS AND BEAMLIN PSS WATER SYSTEMS**

SPARES IN GOOD CONDITION				Updated 2-28-02 by R. Dortwegt
Manufacturer	Serial No.	Location	Range	Calibraton date (date only: item is calibrated and tagged) ("Assigned to" indicates assignment date)
Viatran	219766	Tool box on Storage Ring	0-50 inWC	2/18/2002
Viatran	268287	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	Assigned to D. Croupat 2-27-02
Viatran	279608	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	6/18/2002
Viatran	290337	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	Assigned to D. Croupat 2-27-02
Viatran	298988	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	1/30/2002
Viatran	299378	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	Assigned to D. Croupat 2-27-02
Viatran	310940	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	1/16/2002
Viatran	315845	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	10/25/2001
Viatran	315846	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	10/26/2001
Viatran	315848	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	10/24/2001
Viatran	319865	Cabinet across from 401/L0128 (XFD WATER 1)	0-50 inWC	3/29/2002
Viatran	225785	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 inWC	Assigned to D. Croupat 2-27-02
Viatran	238329	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 inWC	Assigned to D. Croupat 2-27-02
Viatran	283330	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 inWC	Assigned to D. Croupat 2-27-02
Viatran	235327	Cabinet across from 401/L0128 (XFD WATER 1)	0-15 PSI	Assigned to D. Croupat 2-27-02
Viatran	235328	Cabinet across from 401/L0128 (XFD WATER 1)	0-15 PSI	3/7/1996 (brand new)
Viatran	217398	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 PSI	Assigned to D. Croupat 2-27-02
Viatran	217428	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 PSI	Assigned to D. Croupat 2-27-02
Viatran	217657	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 PSI	Assigned to D. Croupat 2-27-02
Viatran	217670	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 PSI	1/31/2002
Viatran	262873	Cabinet across from 401/L0128 (XFD WATER 1)	0-100 PSI	Assigned to D. Croupat 2-27-02
Viatran	215636	Cabinet across from 401/L0128 (XFD WATER 1)	0-125 PSI	Assigned to D. Croupat 2-27-02
Viatran	263003	Cabinet across from 401/L0128 (XFD WATER 1)	0-125 PSI	Assigned to D. Croupat 2-27-02
Viatran	263007	Cabinet across from 401/L0128 (XFD WATER 1)	0-125 PSI	Assigned to D. Croupat 2-27-02
Viatran	217414	Tool box on Storage Ring	0-150 PSI	1/16/2002
Viatran	245537	Bicycle	0-150 PSI	1/15/2002
Viatran	279599	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02

Viatran	288232	Tool box on Storage Ring	0-150 PSI	5/13/1999
Viatran	292040	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	292043	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	299389	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	299390	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	299392	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	299393	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	299396	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	311058	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	Assigned to D. Croupat 2-27-02
Viatran	315849	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	10/31/2001
Viatran	315850	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	10/26/2001
Viatran	315851	Cabinet across from 401/L0128 (XFD WATER 1)	0-150 PSI	10/29/2001
Yokagawa	JEJAWK192	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/9/2002 (factory calibration)
Yokagawa	JEJAWK207	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/10/2002 (factory calibration)
Yokagawa	JEJAWK209	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/10/2002 (factory calibration)
Yokagawa	JEJAWK238	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/10/2002 (factory calibration)
Yokagawa	JEJAWK239	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/10/2002 (factory calibration)
Yokagawa	JEJAWK243	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/10/2002 (factory calibration)
Yokagawa	JEJAWK245	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/11/2002 (factory calibration)
Yokagawa	JEJAWK246	Cabinet - Exp. Floor - Col. 144	0-400 inWC	12/11/2002 (factory calibration)
Yokagawa	12B214757U	Cabinet - Exp. Floor - Col. 144	0-2000psi	11/25/2002 (factory calibration)
Yokagawa	12B214763U	Cabinet - Exp. Floor - Col. 144	0-2000psi	11/25/2002 (factory calibration)
Yokagawa	12B414798U	Cabinet - Exp. Floor - Col. 144	0-2000psi	11/25/2002 (factory calibration)
Yokagawa	12B913496U	Cabinet - Exp. Floor - Col. 144	0-2000psi	11/25/2002 (factory calibration)
SPARES SHIPPED OUT FOR REPAIR BY MANUFACTURER				
Current Status:	Diagnosis complete; regvised P/R in process			
Viatran	219929	Vendor's factory	0-50 inWC	
Viatran	219930	Vendor's factory	0-50 inWC	
Viatran	219937	Vendor's factory	0-50 inWC	
Viatran	219939	Vendor's factory	0-50 inWC	
Viatran	219976	Vendor's factory	0-50 inWC	
Viatran	224310	Vendor's factory	0-50 inWC	
Viatran	224336	Vendor's factory	0-50 inWC	
Viatran	245548	Vendor's factory	0-50 inWC	
Viatran	245562	Vendor's factory	0-50 inWC	
Viatran	288467	Vendor's factory	0-50 inWC	
Viatran	298996	Vendor's factory	0-50 inWC	

Viatran	299385	Vendor's factory	0-50 inWC	
Viatran	299387	Vendor's factory	0-50 inWC	
Viatran	310928	Vendor's factory	0-50 inWC	
Viatran	310936	Vendor's factory	0-50 inWC	
Viatran	310937	Vendor's factory	0-50 inWC	
Viatran	311091	Vendor's factory	0-50 inWC	
Viatran	215585	Vendor's factory	0-100 PSI	
Viatran	215605	Vendor's factory	0-100 PSI	
Viatran	217395	Vendor's factory	0-100 PSI	
Viatran	217412	Vendor's factory	0-100 PSI	
Viatran	218188	Vendor's factory	0-100 PSI	
Viatran	217644	Vendor's factory	0-150 PSI	
Viatran	218197	Vendor's factory	0-150 PSI	
Viatran	219717	Vendor's factory	0-150 PSI	
Viatran	263006	Vendor's factory	0-125 PSI	
Viatran	279589	Vendor's factory	0-150 PSI	
Viatran	279600	Vendor's factory	0-150 PSI	
Viatran	292039	Vendor's factory	0-150 PSI	
UNUSEABLE SPARES TO BE SHIPPED FOR DIAGNOSIS AND REPAIR				
Current Status:	In cabinet awaiting shipment; P/R not created.			
Viatran	218516	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	219531	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	219698	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	219977	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	220111	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	224332	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	229521	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	245563	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	245566	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	288301	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	310931	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	310934	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	311095	Cabinet across from 401/L0128 (XFD WATER 4)	0-50 inWC	
Viatran	217411	Cabinet across from 401/L0128 (XFD WATER 4)	0-150 PSI	
Viatran	310908	Cabinet across from 401/L0128 (XFD WATER 4)	0-150 PSI	